WOVOGLASS



LINER

WovoGlassTM: A WovoLiner® Product

An ultra-flexible liner, uniquely bonded to a seamless impermeable polyurethane coating which is 3x stronger than traditional liners. The circular-knitted construction of polyester and extensible fiberglass reinforcement makes it ideal for transitioning several pipe diameters and lining around multiple bends up to 90°. This liner is manufactured in accordance with ISO9001:2015.

DIMENSION AVAILABILITY: TYPICAL RESIN & ROLLER GAP INFORMATION

WOVOGLASS	TYPICAL INSTALLED THICKNESS	TYPICAL RESIN SATURATION			ADDITIONAL INFO		
PIPE DIAMETER		LITERS PER METER	KG/M IF SG 1.2	LB/FOOT IF SG 1.2	ROLLER GAP	SUPPLY LENGTHS	
3"/70 mm	3.5 mm	0.79	0.94	0.75	9 mm	328′/100m	
4"/100 mm	3.5 mm	1.06	1.27	0.90	9 mm	328′/100m	
6"/150 mm	3.5 mm	1.61	1.93	1.30	9 mm	328′/100m	
8"/200 mm	3.5 mm	2.16	2.59	1.70	9 mm	328′/100m	

INSTALLATION METHODS

	RESIN TYPE			CURING PROCESS				
WOVOGLASS	EP	UP	VE	HOW WATER <176°F	STEAM & AIR <176°F	AMBIENT	WARM WATER	LED CURE
HOT CURE INVERSION	YES	NO	YES	YES	YES	YES	YES	YES
HOT CURE DRAG-IN	YES	NO	YES	YES	YES	YES	YES	YES
DRAG-IN	NO	NO	NO	NO	NO	NO	NO	NO

We recommend that all wovoglass installations should be supported at all positions outside of thepipe being lined. If not a blind shot, it is important to evert the product in longitudinal tension in order to avoidwrinkling. Compatibility of specific resins should be verified.

LINER PREPARATION & INSTALLATION

A suitable holdback should be employed and should be paid out in tension with air or water pressure asbelow. Site circumstances, such as ground water head, should be considered when selecting an appropriateinstallation head.

WOVOGLASS



LINER

WOVOGLASS	MINIMUM INVERSION HEAD (WITH HOLDBACK TENSION)			IVERSION OR HEAD	RECOMMENDED CURE HEAD	
DIAMETER	BAR	PSI	BAR	PSI	BAR	PSI
3"/70+ mm	0.2	3	0.4	6	0.3	4.5
4"/100 mm	0.2	3	0.4	6	0.3	4.5
6"/150 mm	0.2	3	0.3	4.5	0.2	3
8"/200 mm	0.2	3	0.3	4.5	0.2	3

STORAGE/HANDLING:

Avoid extremes of temperature

- Freezing may cause the coating structure to degrade locally, especially areas where the coating is in tension or compression at bends and edges, and immediately adjacent to seam welds.
- Recommended storage temperature 40°F 95°F (4°C 35°C).
- Shelf life at this temperature: in excess of 1 year.

Avoid extremes of humidity

- Very high relative humidity (especially at high temperatures such as tropical countries) will accelerate the degradation, consequently reducing the shelf life.
- Recommended storage humidity 25% rh 65% rh.
- Shelf life at 65%, 95°F (35°C): in excess of 1 year.

Avoid prolonged wet storage

As with high humidity, the coating is more susceptible to degradation at higher temperatures, and even further susceptible if pH of liquid in contact is significantly above or below 45°F (7°C). Wet storage is not recommended.

Avoid direct sunlight

Prolonged exposure to the sun's ultraviolet light will accelerate the degradation of the coating. Store away from direct sunlight, preferably in dark conditions.

Mechanical damage should be avoided

- Ensure that liner is not placed directly onto grit or gravel floor sweep and cover floor first.
- Ensure personnel are instructed not to walk on or smoke around the liner.
- Handle with care and always ensure safe transport.
- Ensure any rollers are clean, and the liner is not in contact with any sharp edges or snags anywhere during use.

Chemical attack

Avoid prolonged contact with solvents and chemicals.

Call technical support with additional questions at +1 (734) 744 5557

Disclaimer: The information contained herein is offered without charge for use by technically qualified personnel at their discretion and risk. All statements, technical information and recommendations contained herein are based on test and data which we believe to be reliable, but the accuracy or completeness thereof is not guaranteed and no warranty of any kind is made with respect thereto. Exact coating type and thickness depend on the specific types of resin being used. Always read, understand, and comply with hazard warnings described in the products' Safety Data Sheet(s) before use.